




TECHNICAL SHEET



NON-PRESCRIPTION EYE PROTECTION

B-92 SPECTACLES

DESCRIPTION AND COMPOSITION

Very light, front and ocular made of one piece, complete spectacle made in polycarbonate.

Upper part with ciliary seal which obstructs that particles pass through to the eye.

Temples with lateral protection made in polycarbonate. With 6 vertical slats which favour anti-fogging.

Dielectric: with no metal parts.

Ocular of 2mm thickness and nominal dimensions of 152x60mm.

Can be used as visitor glasses and worn over prescription spectacles

TECHNICAL DATA

		MARKING
900.375	Clear polycarbonate	CE MEDOP 1 F 166 F
900.376	Clear polycarbonate Anti-Scratching Treatment	CE MEDOP 1F 166 F
900.377	Clear polycarbonate Anti-Scratching and Anti-FoggingTreatment	CE MEDP 1F 166 F
900.378	Welding Polycarbonate DIN 3	CE 3 MEDOP 1F 166 F
900.380	Welding Polycarbonate DIN 5	CE 5 MEDOP 1F 166 F
900.384	Grey Solar Polycarbonate	CE 5-31 MEDOP 1 F
900.386	Optol Polycarbonate	CE 2-1.2 MEDOP 1F

- 1: Optical Class.
- F: High velocity, low energy impacts.
- 3 and 5: Welding protection.
- 5-3,1: Solar Protection.
- 2-1,2: Ultraviolet Protection

APPLICATIONS

Depending on version: Outdoors activities, painting, textile, plastics, warm working environments, forest work, welding etc.



UNE EN-166



UNE EN-166
UNE EN-170
UNE EN-172



UNE EN-166
UNE EN-170



UNE EN-166
UNE EN-169



TECHNICAL SHEET

NON-PRESCRIPTION EYE PROTECTION

B-92 SPECTACLES

MAINTENANCE /STORAGE/ CARE

For an adequate maintenance of your glasses keep them in a clean and dry place, inside an appropriate case.

INSTRUCTIONS/ USE / USAGE METHOD

How to clean polycarbonate: Use tepid water and neutral soap, without abrasives or disolvents. Clean with water and dry with a soft cloth. We also recommend MEDOP ANTI-FOG CLEANING SPRAY.

Protectors must be checked periodically and replaced if they are damaged.

Make sure these protectors correspond with the risk to prevent at work.

PRESENTATION

Units of Sale:
12 unit boxes.
25 box carton.



STANDARD AND CERTIFICATION

UNE EN 166; UNE EN 170; UNE EN 171; UNE EN 172; UNE EN 169